


GMCF-45 45G7B3

45MHz 4 pole crystal filter with 7.5kHz 3dB bandwidth

- Custom specifications available
- Fundamental or 3rd overtone modes
- Comprehensive stocks




CONFIGURABLE OPTIONS	
Parameter	Option Code
Package	
Any	
UM-1/3Lx2 (leaded)	
UM-5/3Lx2 (leaded)	
UM-1JN/3Lx2 (SMT)	
UM-5JN/3Lx2 (SMT)	



SPECIFICATIONS

PACKAGE DRAWING

Centre frequency	45.0MHz
Dimensions	Package options available - see Package Drawing
Operating temperature range	-20 to +70°C
Number of poles	4
Pass band	-3dB @ ±3.75kHz min
Attenuation band	-30dB @ ±12.5kHz max
In-band ripple	1.0dB max
Insertion loss	3.0dB max
Guaranteed attenuation	-65dB max ±300 ~ ±1000kHz
Termination	2000Ω // -0.5pF
Coupling capacitance (C _C)	1.0pF
Package style	UM-1/3Lx2, UM-5/3Lx2 (through-hole) UM-1JN/3Lx2, UM-5JN/3Lx2 (SMT)




UM-1JN/3L

UM-5JN/3L

12.50 max

10.50 max Dimensions in mm



8.00 max

6.00 max

UM-5/3L




ORDERING INFORMATION

To request a quotation for the GMCF-45 45G7B3 please use the configurable options form to choose the options you require and then submit your configured product to our team. Our expert advisers are always happy to help with your requirements and can be contacted on +44 1460 256 100 or at sales@golledge.com.

Following product selection you will be issued with a seven character Golledge part number. Your Golledge part number is the internationally accepted Golledge manufacturing part number (MPN) that should be used for all project documentation, including bills of materials (BoMs) and purchase orders.

If you have any queries regarding any of our documentation our dedicated sales team will be happy to help.

TAPE & REEL SPECIFICATION



UM-1J - A:330 B:24 C:14.1 D:8.4 E:12 F:4.6 G:80 H:21 UM-5J - A:180 B:24 C:12.5 D:8.4 E:12 F:4.4 G:60 H:21



HANDLING & STORAGE

CONSTRUCTION




Human Body Model (HBM) 1A (250V to <500V)

Resistance weld



Moisture Sensitivity Level (MSL): 1 (or not applicable)

Bulk-packed 4-pole filters: Pair alignment when boxed.



These filters are individually matched pairs. One filter is composed of two physical units, which have been factory-matched for optimum performance.

DO NOT MIX. Unmatched pairs will offer impaired performance.

For filters supplied in boxes, please refer to the above diagram.

Matched pairs may also be supplied in individual bags.



COMPLIANCE



Lead-free (< 0.1% by weight)



RoHS compliant with no exemptions. See our

declaration



REACH compliant. See our statement



Au Ta Sn W Free of conflict minerals. See our declaration



Free of Halogens. <u>See our declaration</u>



Free of Ozone-depleting substances. <u>See our</u>

declaration